



Body, Flare cone, Gasket, and Cutting ring adapter material	Stainless steel 1.4404/EN10272 (AISI316L)
Flare material	Stainless steel 1.4305/EN 10088 (AISI303)
O-ring material	NBR70
Bolt material	DIN912-A4-80
Mass	6 kg
Working pressure	140 bar
Test pressure	210 bar