

Kidde[®] ECS[™] Fire Suppression System

Designed for use with 3M[™] Novec[™] 1230 Fire Protection Fluid



Effective: June 2018

K-45-2670 Rev AA

Cylinder Data Sheet (Marine Applications)

FEATURES

- *UL Listed and USCG Certified for use with Novec 1230 Fire Protection Fluid Systems*

Part Number	Fill Range		Empty Weight		Gross Weight				With LLI	Height		Diameter		Volume	
	lb.	kg	lb.	kg	Min. Fill		Max. Fill			in.	cm	in.	cm	ft. ³	m ³
45-200010-001	6 to 11	2.7 to 5.0	25	11	31	14.1	36	16.3	No	17.3	44	7.07	18	0.167	0.0047
45-200020-001	12 to 23	5.4 to 10.4	31	14	43	19.5	54	24.5	No	24.97	64	7.07	18	0.289	0.0081
45-200040-001	20 to 40	9.1 to 18.1	38	17	58	26.3	78	35.4	No	26.76	68	9.00	23	0.572	0.0162
45-200070-001	35 to 70	15.9 to 31.8	52	24	87	39.5	132	59.9	No	38.83	99	9.00	23	1.000	0.0283
45-200121-001	63 to 125	28.6 to 56.7	98	45	161	73.0	223	101.2	Yes	35.93	92	12.75	33	1.788	0.0506
45-200125-001	63 to 125	28.6 to 56.7	98	45	161	73.0	223	101.2	No	35.93	92	12.75	33	1.788	0.0506
45-200200-001	100 to 200	45.4 to 90.7	133	60	233	105.7	333	151.0	No	52.75	134	12.75	33	2.859	0.0810
45-200201-001	100 to 200	45.4 to 90.7	133	60	233	105.7	333	151.0	Yes	52.75	134	12.75	33	2.859	0.081
45-200350-001	175 to 350	79.4 to 158.8	201	91	376	170.6	551	249.9	No	58.36	149	16.00	41	5.000	0.1416
45-200351-001	175 to 350	79.4 to 158.8	203	92	378	171.5	551	249.9	Yes	58.36	149	16.00	41	5.000	0.1416
45-200600-001	300 to 600	136.1 to 272.1	362	165	662	300.3	962	436.4	No	58	147	22.00	56	8.680	0.2460
45-200601-001	300 to 600	136.1 to 272.1	362	165	667	302.5	962	436.4	Yes	58	147	22.00	56	8.680	0.2460
45-200900-001	455 to 910	206.3 to 412.7	505	230	960	435.5	1415	641.8	No	70	178	24.00	61	13.00	0.3680
45-200901-001	455 to 910	206.3 to 412.7	505	230	960	435.5	1415	641.5	Yes	70	178	24.00	61	13.00	0.3680

Note: See the corresponding Design, Installation, Operation and Maintenance Manual (P/N 06-236559-001) for additional information.

EXPORT INFORMATION (USA)

Jurisdiction: EAR

Classification: EAR99

This document contains technical data subject to the EAR.

KIDDE is a registered trademarks of Kidde-Fenwal, Inc. or its parents, subsidiaries or affiliates. Novec and 3M are trademarks of the 3M Company.

©2018 Kidde-Fenwal, Inc.

This literature is provided for informational purposes only. KIDDE-FENWAL, INC. believes this data to be accurate, but it is published and presented without any guarantee or warranty whatsoever. KIDDE-FENWAL, INC. assumes no responsibility for the product's suitability for a particular application. The fire suppression system design, installation, maintenance, service and troubleshooting must be performed by trained, authorized Kidde Fire Systems distributors for the product to work correctly. If you need more information on this product, or if you have a particular problem or question, contact KIDDE-FENWAL, INC., Ashland, MA 01721 USA. Telephone: (508) 881-2000.

Kidde Fire Systems
400 Main Street
Ashland, MA 01721
Ph: 508.881.2000
Fax: 508.881.8920
www.kiddefiresystems.com