

# Kidde Fire Systems

## ADS™ Cylinder Component Datasheet



### 600 lb. (243 L) Cylinder and Valve Assemblies with Fluoro-K™ Fire Suppression Clean Agent

Effective: November 2023  
K-45-903 Rev AB

#### FEATURES

- Well Suited for Complicated Pipe Networks and Large Area Coverage with Minimal Room for Cylinder Storage
- 3-Inch Valve Outlet
- 300 lb. to 600 lb. Fill Capacity
- Agent Cylinder Liquid Level Indicator
- Uses one or two Nitrogen Drivers
- UL Listed, File Number 4674
- FM Approved
- For RoHS Compliance, See the Individual Component Datasheets

#### DESCRIPTION

Kidde Fire Systems Advanced Delivery Systems (ADS™ system) are Underwriters Laboratory (UL) listed and Factory Mutual (FM) approved. These systems are designed for total flooding in accordance with NFPA 2001, *Standard on Clean Agent Extinguishing Systems*. These systems have been tested to UL 2166, *Standard for Safety; Standard for Halocarbon Clean Agent Extinguishing System Units*, and Factory Mutual 5600, *Examination Standard for Clean Agent Extinguishing Systems*.

The ADS system uses a unique method for propelling the Fluoro-K™ Fire Suppression Clean Agent (herein referred to as “agent”) from the storage cylinder, through the piping system and out of the discharge nozzles. Nitrogen gas pressure from a separate storage cylinder is introduced into the vapor space of the agent cylinder at a controlled rate. This nitrogen pressure acts to propel the agent through the pipe at a higher flow rate. It can also propel the agent farther through the pipe network allowing for the placement of storage cylinders remotely from the protected hazard.

The ADS system is extremely well-suited to applications involving remote agent storage and situations which limit the maximum pipe size to be used. The system is capable of using smaller pipe sizes to discharge large quantities of Agent.

#### OPERATION

When a control head actuates the nitrogen cylinder discharge valve(s), the nitrogen pressure actuates the agent cylinder discharge valve and pressurizes the cylinder. Agent is then propelled by its own vapor pressure and the nitrogen pressure through the discharge valve and into the system pipe network. The liquid agent travels through the system pipe network at a high flow rate.



#### OPERATING RANGE LIMITATIONS

- The operating temperature range for all components used in the ADS system is 32° to 130°F (0° to 54°C)
- The agent cylinder operating temperature must be between 60° to 80°F (16° to 27°C) for unbalanced pipe network systems.

#### INSTALLATION

The ADS system installation is based on the requirements of NFPA 2001, *Standard on Clean Agent Extinguishing Systems*, Current Edition.

#### ASSEMBLY:

Both the nitrogen drivers and agent storage cylinders are to be installed in the vertical position only. The nitrogen driver is located to the immediate right apart from the agent cylinder. The nitrogen driver cylinder is connected to the agent cylinder by using the nitrogen transfer components. The nitrogen transfer components used depends upon whether the system uses one or two nitrogen drivers. The 3/4-in. transfer fitting connects into the orifice fitting. The orifice fitting is a custom fitting that is designed to regulate the nitrogen pressure flow required for the specific system. The orifice fitting then connects into the 3/4-in. check diffuser assembly to diffuse the nitrogen in a horizontal pattern.




Figure 1. Single Cylinder Installation Dimensions, 600 lb. (243 L) Cylinder




Figure 2. Dual Driver Installation, Vertical Mounting for 600 lb. (243 L) Systems

**ACTUATION:**


When using the agent, the ADS system can use one or two drivers with the 600 lb. (243 L) agent cylinder. Use the flow calculation software to determine which setup is applicable for the design.

**Single Driver Systems**

The control head is attached to the nitrogen driver by means of electric, cable, lever, or pneumatic devices. The actuating of the agent cylinder is done upon transfer of nitrogen from the driver cylinder using the actuation assembly kit (P/N 06-129882-001).

Assembly includes:

- Nitrogen transfer fitting
- 1/8-in. flex loop
- 1/8-in. flare fitting
- 1/8-in. branch tee
- 1/8-in. Schrader fitting and cap
- Pressure operated control head



**Single Driver Actuation Assembly Ordering Information**

**06-129882-001 Contains:**

| Item No. | Qty. | P/N           | Description   |
|----------|------|---------------|---|
| 1        | 1    | 06-236124-001 | Nitrogen Transfer Fitting                           |
| 2        | 1    | 82-878737-000 | Pressure Operated Control Head (Pneumatic Actuator) |
| 3        | 1    | 06-118191-001 | Fitting Flared 1/8-in. x 1/4-in.                    |
| 4        | 1    | 06-118193-001 | 3/16-in. Flexible Actuation Hose                    |
| 5        | 1    | 06-118192-001 | 1/8-in. Branch Tee                                  |
| 6        | 1    | WK-263303-000 | 1/8-in. Schrader Valve                              |
| 7        | 1    | WK-263304-000 | 1/8-in. Schrader Valve Cap                          |


For more information, refer to datasheet K-85-103

**Dual Driver Systems**

The control head is attached to the primary nitrogen driver by means of electric, cable, lever or pneumatic devices. The actuating of the second nitrogen driver and agent cylinder is done upon transfer of nitrogen from the primary driver cylinder using the actuation assembly kit (P/N 06-129985-001).

Assembly includes:

- Nitrogen “Y” Transfer Fitting
- 1/8-in. Flex Loop
- 1/8-in. Flare Fitting
- 1/8-in. Branch Tee
- 1/8-in. Schrader Fitting and Cap
- Pressure Operated Control Head
- 3/4-in. Nipple (Hex)



**Dual Driver Actuation Assembly Ordering Information**

**06-129985-001 Contains:**

| Item No. | Qty. | Part Number   | Description   |
|----------|------|---------------|---|
| 1        | 1    | 06-236260-001 | Nitrogen Transfer "Y" Fitting                       |
| 2        | 1    | 82-878737-000 | Pressure Operated Control Head (Pneumatic Actuator) |
| 3        | 2    | 06-118191-001 | Fitting Flared 1/8" x 1/4"                          |
| 4        | 1    | 06-118193-001 | 3/16" Flexible Actuation Hose                       |
| 5        | 1    | 06-118192-001 | 1/8" Branch Tee                                     |
| 6        | 1    | WK-263303-000 | 1/8" Schrader Valve                                 |
| 7        | 1    | WK-263304-000 | 1/8" Schrader Valve Cap                             |
| 8        | 1    | 06-118330-001 | 3/4" Nipple   |

For more information, refer to datasheet K-85-110

## MAINTENANCE

According to NFPA standards, the following inspection and/or maintenance procedure must be scheduled as listed below and performed upon the occurrence of any event, which might affect the reliability of the system. For more information, see the corresponding DIOM manual. Perform preventive maintenance per the following table:

| Schedule       | Requirement   |
|----------------|---|
| Weekly         | Check nitrogen cylinder pressure  |
| Monthly        | Inspect hazard area system components   |
| Semi-Annually  | Test pressure switches  |
|                | Test electric control heads   |
|                | Check agent cylinder weights  |
| Every 2 Years  | Blow out distribution piping  |
| Every 5 Years  | Agent and nitrogen cylinder and flexible hose hydrostatic pressure test and/or inspection |
| Every 15 Years | Rebuild agent cylinder valves   |

## RECONDITIONING

After a system has been discharged, contact your local authorized Kidde Fire Systems Distributor to recondition the system. Please reference the corresponding DIOM manual for the appropriate reconditioning kit.

## SPECIFICATIONS

| Element                            | Agent Storage Container<br>(P/N: 45-500601-901) |               | Nitrogen Driver (P/N: 85-504070-001) |                           |
|------------------------------------|---|---------------|--------------------------------------|---------------------------|
|                                    | Imperial  | Metric        | Imperial                             | Metric                    |
| Fill Range                         | 300 to 600 lb.                                  | 136 to 272 kg | Factory Filled to 1800 PSIG          | Factory Filled to 124 bar |
| Height of Discharge Port (Center)* | 50.5 in.  | 128.3 cm      | 62 in.                               | 1575 mm                   |
| Diameter                           | 22.0 in.  | 56.0 cm       | 10.5 in.                             | 267 mm                    |
| Internal Volume                    | 8.08 cu ft                                      | 0.25 cu m     | 4070 cu. in.                         | 0.0667 m3                 |
| Empty Weight                       | 362.0 lb  | 164.0 kg      | 186 lb.                              | 84.4 kg                   |
| Temperature Range                  | 32°F to 130°F                                   | 0°C to 54°C   | 32°F to 130°F                        | 0°C to 54°                |

\*For Nitrogen Drivers, the center is the top of the valve/cylinder assembly.

Note: The Nitrogen used is A-A-59155 Grade A, Type 1.

## ORDERING INFORMATION FOR AGENT CYLINDER AND DRIVERS

| Part Number    | Description                             |
|----------------|---|
| 45-500601-901  | 600 lb. (243 L) Agent Storage Container |
| 85-504070-001* | 4070 cu. in. Nitrogen Driver Cylinder   |
| 85-111540-001  | Supervisory Pressure Switch             |
| 85-111540-100  | ATEX Supervisory Pressure Switch        |

\*Note: Use the flow calculation software to determine the number of drivers needed for each 600 lb. agent cylinder.

## MANUALS

| Manual   | P/N           |
|--|---------------|
| Kidde Fire Systems ADS™ Fire Suppression System for use with Fluoroketone Fire Suppression Agents Design, Installation, Operation and Maintenance Manual               | 06-237256-001 |
| Kidde Fire Systems ADS™ Fire Suppression System Marine Series for use with Fluoroketone Fire Suppression Agents Design, Installation, Operation and Maintenance Manual | 06-237257-001 |

### EXPORT INFORMATION (USA)

Jurisdiction: EAR  
Classification: EAR99

This document contains technical data subject to the EAR.

All trademarks are the property of their respective owners.

This literature is provided for informational purposes only. KIDDE-FENWAL, INC. believes this data to be accurate, but it is published and presented without any guarantee or warranty whatsoever. KIDDE-FENWAL, INC. assumes no responsibility for the product's suitability for a particular application. The fire suppression system design, installation, maintenance, service and troubleshooting must be performed by trained, authorized Kidde Fire Systems distributors for the product to work correctly. If you need more information on this product, or if you have a particular problem or question, contact: KIDDE-FENWAL, INC., Ashland, MA 01721 USA, Telephone: (508) 881-2000.