


# CO<sub>2</sub> Component Description

## Pressure vs. Temperature for Carbon Dioxide Cylinders



Effective: June 2016  
K-81-1031 Rev AC



Percent of Water Capacity =

$$\frac{\text{Rated CO}_2 \text{ Capacity of Cyl. in Lb.}}{\text{Water Capacity of Cyl. in Lb. at 60}^\circ\text{F}} \times 100$$

Critical Temperature of CO<sub>2</sub> = 88°F

| RATED CO <sub>2</sub> CAPACITY OF CYL. IN LB | PERCENT WATER CAPACITY |
|--|------------------------|
| 25   | 67                     |
| 35   | 64                     |
| 50   | 60                     |
| 75,100                                       | 68                     |

### EXPORT INFORMATION (USA)

Jurisdiction: EAR  
US ECCN: EAR99

All trademarks are the property of their respective owners.

This literature is provided for informational purposes only. KIDDE-FENWAL, INC. assumes no responsibility for the product's suitability for a particular application. The product must be properly applied to work correctly. If you need more information on this product, or if you have a particular problem or question, contact KIDDE-FENWAL Inc.