

MANUAL CALL POINT WITH SELFVERIFY - BF-501/EX

Interactive fire detection systems Product Datasheet

Technical specifications and instructions

Features

- Break glass unit for use in harsh environmental conditions
- Weather proof
- Corrosion resistant GRP
- Protection degree IP66
- Short circuit isolator in each unit
- Automatic addressing
- Proven technology
- With SelfVerify function for reduced maintenance/testing and increased reliability
- Designed to meet the requirement of the major maritime classification societies

Description / Application

BF-501/EX is a manual call point for use in hazardous area zone 0, 1 or 2. It must be connected to the approved barrier BZ-500. The call point has been designed for use with Autronica's interactive fire detection systems, and comprises the SelfVerify function. This function ensures the highest grade of reliability and the lowest degree of manual testing, because all units comprising this function are automatically self-tested once every 24 hours.

The high IP degree and mechanical strength of the enclosure makes the call point suitable for outdoor applications in industrial, maritime and offshore installations.

The call point must be installed according to local regulations which normally means along escape routes, landings and exits.

Principle

Break glass operation, releasing alarm switch.
Reset when a new glass is mounted.

SelfVerify: the call point's ability to initiate alarms is regularly checked.




Versions

- BF-501* Manual call point with SelfVerify
- BF-501/EX Manual call point with SelfVerify. Ex ia version for use in zone 0, 1 and 2
- BF-501/N* Manual call point with SelfVerify. Ex ic version for use in zone 2 only

* See separate datasheet

Schedule Drawing

No modifications permitted
without reference to the
Notified Body


Technical specifications	
Weight	1,2 kg
Material	Glass reinforced polyester
Colour	Red
Voltage	10 - 27 VDC
Current consumption, stand by:	0,3 mA
Environm. requirement	EN 54
Degree of protection	IP66*
Working temperature	-25 - +70 °C
Storage temperature	-55 - +70 °C
Cable inlets	2 x M20
Maintenance	Replace broken glass
Service	Replace if faulty
Certificates	See website
Notified body	Nemko ID No. 0470 CSA
Type examination certificates	NEMKO 03ATEX218X IECEX NEM 11.0009X
Directives and standards	<p>2014/34/EU (ATEX) EN 60079-0:2012 EN 60079-11:2012 IEC 60079-0:2011 IEC 60079-11:2011 2014/30/EU (EMC) Immunity: EN 50130-4:2011 Emission: EN 61000-6-3:2001</p> <p>CAN/CSA-C22.2 No. 0-10 CAN/CSA-C22.2 No. 205-12 CAN/CSA-60079-0-11 CAN/CSA-60079-1-11 CAN/CSA-60079-11-11 CAN/CSA-C22.2 No. 60529-05</p> <p>UL 464, 9th Edition UL 60079-0, 5th Edition UL 60079-1, 6th Edition UL 60079-11, 5th Edition</p> <p>ANSI/IEC 60529:2004 ANSI/ISA-60079-26: 2011</p>
Ex parameters	<p> II 1G Ex ia IIC T5 Ga Class 1, Zone 0, AEx ia IIC T5 Ga U_i = 15,75V I_i = 63,5mA C_i = 21,6nF L_i = 0 P_i = 0,44W</p> <p>Warning: Do not rub.</p>

*requires approved cable glands and/or plugs of minimum the same IP level.

Product Name	Part number	Description
BF-501/EX	116-BF-501/EX	Manual call point with 2 glands (type 116-6571-011.1920)
Accessories		
	116-6571-011.1920	GLAND ST M20X1,5 PG13,5 (1 pcs)

Dimensions

Dimensions: HxWxD = 126x120x75mm



Connections

